SZ-BOLT BTG-10R Tactical Red Laser Tactical Red Laser Tactical Red Laser Tactical Red Laser Tactical Communications Red Dot Laser FDA Class IIIa

Safety First

The BTG-10R Red Laser is "Armed" when the battery is installed and begins lasing upon operation of the constant on/off switch.

If in doubt, always point the aperture of the laser toward the ground before testing battery or switches.

FDA Safety Class Illa

FDA Class Illa lasers can be dangerous. Class Illa lasers can cause temporary visual effects such as flash blinding, which could distract or startle the person exposed. The risk of injury is very small when Class Illa pointers are used responsibly because natural body motion of a person holding the pointer or motion of a person who might be exposed makes it difficult to expose the eyes for a long period of time. People also have a natural aversion to bright lights and are likely to close their eyes and turn their heads if exposed. These natural reactions reduce possible injury.

Laser Radiation. Avoid direct eye exposure.

Simple

Precision Visual Comm


Designed for Intense Field Duty:

Water Resistant Shock Resistant Constant On/Off Lightweight Power Lockout

Battery Installation

Switch







Laser Aperture

Unscrew switch counter clockwise. Insert Qty (1) 3v lithium battery with tip (+) toward switch.

Z-Bolt BTG-10R Box Contents

Qty 1 BTG-10R Tactical Red Laser

> Qty 2 CR123A 3V Lithium Battery 1500 maH







Qty 1 SMP-10 Modular Pouch



Parts, Accessories, Batteries, Rail Mounts: Primary Contact: John Mueller, Managing Director 503-867-1617/ Fax: 603-386-6644 John@Z-Bolt.com www.Z-Bolt-Laser-Systems.com Portland, Oregon, 97266, USA

> Copyright 2021, All Rights Reserved. Z-BOLT is a registered trademark of Beam of Light Technologies, Inc. [BTG-10R-Insert-JMM-02-24-21]

BTG-10R SPECIFICATIONS

Battery

Tactical Red Laser (BTG-10R) Wavelength 635nm, Red Output Power 5 mW, FDA Class Illa Operating Current <300 mA Power Source Qty 1 CR123A Lithium Battery, 3V DC Output Mode Constant Wave Beam Diameter at Source 1.1 mm Beam Divergence 1.0 mRad Switches (1) Constant On/Off Tactile Switch Weight 108 grams/3.8 oz with Switch and CR123A Lithium Battery Installed Body Tube Material T6061 Aluminum Alloy Surface Anodized Black Matte Finish

Overall Dimensions: L 126mm x W 25.4mm x H 25.4mm Warranty 2 Years from Date of Purchase





Z-Bolt® Laser Devices Weapon Lights & IR Illuminators Forensic Laser & LED Light Sources

ACAL Lasers & IR Illuminators

Blazer Weapon Lights









Multi-Function Dot & Line Trip Wire Illuminators





Twist Head for Dot or Line Function - Green or Infrared Variants . . .



Field Utility Laser Pointers - Reduce Operational Errors



Precise Non-Verbal Communications

Red Blue Green Infrared

Hand-Held FDA Class 1
Civilian Legal & EYE-SAFE

FDA CLASS IIIa & ANSI 3R Dot & Beam Laser POINTERS

Forensic Imaging Lasers

EBI. EBI.

400mW Green Laser
10W Blue LED Light
2x Filtered Glasses
Battery Charger + Batts
Optical Cleaning Kit
Injection Molded Case

Blue & Multi-Color LED Lights





Z-Bolt® Forensics - Alternate Light Sources

Call or Email for Details: 503-867-1617 John@Z-Bolt.com